Services

Customized Sensors & Components Made by Endress+Hauser





High quality for your application and products

The development of technical products and devices is becoming increasingly complex. Companies who wish to develop innovative products quickly and cost-effectively must overcome this complexity. In so doing, they must be able to rely on suppliers of critical process components for their end products. A technology partnership with Endress+Hauser customer-specific Sensors&Components division allows you to concentrate fully on your core product.

We will supply you with the best fitting sensor for your application. We will be at your side from the initial idea to the consulting phase and joint development effort, through to the manufacture of prototypes and finally series production in the required quantities. Release and approval processes as well as the required certification are key elements of our comprehensive service.









Serial production

Maximum quality and product safety as sensors are produced under clean room conditions.

High level of automation ensures high and consistent quality.

Coordinated purchase quantities and batch sizes.

Complete traceability of core components.

Review

Zero-defect strategy in serial production: Testing of all the individual components as well as the end product.

Optimum supply chain

Just-in-time delivery and in the quantity required by the specified deadline.

Support for the entire logistics chain worldwide and customer-specific supplychain concepts.



Understand requirements to find suitable solutions

Our success as a supplier of measuring instruments is based, among other things, on the technological properties of the sensors. The performance of the sensor can be used sustainably in many applications and sectors – whether independently, in the form of a customer-specific pressure transducer or in the mounting and assembly process of the pressure sensor only. Always according to your wishes.

With our high technical competence, far-reaching development experience and reliability in every respect, we understand your individual task and transfer it into convincing technical solutions for your application.

Close, personal and long-term cooperation is an essential base for a mutual success.



Capacitive Ceramic Pressure Sensor: Our basic technology for your success

Constituting the "core element" of pressure instruments, the Ceracore capacitive ceramic pressure sensor guarantees cost effective, reliable and safe process control in millions of Endress+Hauser pressure instruments and transducers in customized applications. The new sensor offers a high performance, more flexible adaptation to your application and configuration capabilities in line with your application. The new generation of the Ceracore pressure sensors guarantees safe measurements and special stability.

Safety/Approvals

- Self-monitoring sensor for the highest degree of safety
- Communication via safe protocols
- Good EMC resistance
- Approval capability, e.g. ATEX
- RoHS conformity
- FDA-listed materials

Application-specific configuration

- Sensor preconfigured at the factory site (damping, turn-down, measuring range, ...)
- Adjustable measuring rate for optimum resolution/ power consumption
- Option of configuration by customer
- Additional output of temperature signal
- Power consumption <1.6 mA</p>
- Different sizes (diameters: 17.5 mm and 32.4 mm)

- Metallic active solder connection of the ceramic sensor substrate and diaphragm
- Metallic coating of the sensor substrate for improved EMC and reduced installation sensitivity
- Media wetted parts are produced of ultra-pure ceramics (99.9 % Al₂O₃), highly resistant against the most varied process media and chemically neutral
- The Ceracore sensor is a dry sensor without oil filling for pressure transmission and it is highly vacuum resistant
- High overload resistance
- Linearized and temperature-compensated output signal
- Low measuring ranges available
- Reference accuracy: $\leq 0.1 \%$

Communication

- Analog output signal
 - Voltage output ratiometric
 - Voltage output absolut
- Digital output signal
 - SPI interface
 - UART interface
- Digital and analog output signal may be combined
- Switching output
- Temperature output



Technology

The sensor is based on the capacitive measuring principle. The substrate and the diaphragm serve as components of a capacitor. If pressure is applied to the sensor, the distance between the two electrodes changes due to the deflection of the diaphragm. This leads to a change in capacitivy which is converted into a nominated electric output signal via an ASIC. (Application Specific Integrated Circuit)

Sensor cross section Ceracore USC30



Capacitive ceramic pressure sensors

Ceracore USC30 and USC70 form the basis of all customized pressure transducers. They differ in the size of the sensor and thus the dimensions of the completed pressure transducer. You have the option of developing the housing and process connections by yourself. In that case, we would be pleased to supply our capacitive ceramic pressure sensors configured according to your specifications. We could also supply you with the mounting parts for a perfect fit.

Ceracore USC30

Capacitive ceramic pressure sensor for absolute and gauge pressure measurement.

Design size External diameter: 17.5 mm

Standardized measuring ranges

- 0...100 mbar / 10 kPa / 1.5 psi, overload range: 4 bar / 400 kPa / 60 psi
- 0...200 mbar / 20 kPa / 3 psi, overload range: 5 bar / 500 kPa / 75 psi
- 0...400 mbar / 40 kPa / 6 psi, overload range: 6 bar / 600 kPa / 90 psi
- 0...1 bar / 100 kPa / 15 psi, overload range: 10 bar / 1 MPa / 150 psi
- 0...2 bar / 200 kPa / 30 psi, overload range: 18 bar / 1.8 MPa / 270 psi
- 0...4 bar / 400 kPa / 60 psi, overload range: 25 bar / 2.5 MPa / 375 psi
- 0...10 bar / 1 MPa / 150 psi, overload range: 40 bar / 4 MPa / 600 psi
- 0...20 bar / 2 MPa / 300 psi, overload range: 40 bar / 4 MPa / 600 psi
- 0...40 bar / 4 MPa / 600 psi, overload range: 60 bar / 6 MPa / 900 psi
- 0...100 bar / 10 MPa / 1500 psi, overload range: 150 bar / 15 MPa / 2,250 psi*

Operating conditions

- Process temperature: -20...+80°C (extended temperature range* -40...+125°C)
- Ambient temperature: -20...+80°C (extended temperature range* -40...+125°C)
- Storage temperature: -40...+125°C
- Turn-Down possible up to 5:1**

Output signal and energy supply

- Supply voltage: 2.9 to 5.5 V DC
- Power consumption: <1.6 mA
- Ratiometric or absolute analog output signal
- Digital interface: UART or SPI
- Pressure signal: 24 bit
- Temperature signal (optional): 16 bit
- Measuring rate: 1.25 to 80 ms
- Reference accuracy: ≤0.1 %



* On request

** Specifications at turn-down according to technical specification (TI)

Ceracore USC70

Capacitive ceramic pressure sensor for absolute and gauge pressure measurement.

Design size External diameter: 32.4 mm

Standardized measuring ranges

- 0...100 mbar / 10 kPa / 1.5psi, overload range: 4 bar / 400 kPa / 60 psi
- 0...250 mbar / 20 kPa / 3 psi, overload range: 5 bar / 500 kPa / 75 psi
- 0...400 mbar / 40 kPa / 6 psi, overload range: 8 bar / 800 kPa / 120 psi
- 0...1 bar / 100 kPa / 15 psi, overload range: 10 bar / 1 MPa / 150 psi
- 0...2 bar / 200 kPa / 30 psi, overload range: 18 bar / 1.8 MPa / 270 psi
- 0...4 bar / 400 kPa / 60 psi, overload range: 25 bar / 2.5 MPa / 375 psi
- 0...10 bar / 1 MPa / 150 psi, overload range: 40 bar / 4 MPa / 600 psi
- 0...40 bar / 4 MPa / 600 psi, overload range: 60 bar / 6 MPa / 900 psi

Operating conditions

- Process temperature: -20...+80°C (extended temperature range* -40...+125°C)
- Ambient temperature: -20...+80°C (extended temperature range* -40...+125°C)
- Storage temperature: -40...+125°C
- Turn-Down possible up to 5:1**

Output signal and energy supply

- Supply voltage: 2.9 to 5.5 V DC
- Power consumption: < 1.6mA
- Ratiometric or absolute analog output signal
- Digital interface: UART or SPI
- Pressure signal: 24 bit
- Temperature signal (optional): 16 bit
- Measuring rate: 1.25 to 80ms
- Reference accuracy: $\leq 0.1 \%$



* On request

** Specifications at turn-down according to technical specification (TI)

Customized pressure transducer: The solution for pressure measurement of liquid and gaseous media

The core element of the modular UTC30 is the USC30 capacitive ceramic sensor. The pressure transducer UTC30 is available in different housing variants up to a complete customer-specific transducer. The process connection and the electrical connection are freely configurable. Every pressure transducer is individually temperature compensated and linearized at the factory.

Your benefits

- Dry capacitive ceramic sensor with high-purity (99.9%) Al₂O₃ ceramic diaphragm
- High overload resistance
- Very good long-term stability
- High corrosion resistance
- Absolute and relative measuring ranges from 0...0.1 bar (0...1.5 psi) to 0...100 bar (0...1500 psi)
- Reduced installation effects through optimized AVT
- Highly automated manufacturing processes
- Factory adjustment of zero point and span

Safety/Approvals

- ATEX / IECEx component approvals
- RoHS / REACH compliant
- Materials in contact with the process suitable for FDA requirements or hygiene applications

Design/mechanics

- Open modular system
- Adapter concept for different process connections
- Castable design
- The back of the module can be welded or screwed
- Customized closed versions are possible

Electrical connection

- Socket strip 2x5 pins (1.27 mm pitch)
- Pin strip 2x5 pins (2.54 mm pitch)
- Customized versions are possible

Output signals

- Digital: SPI or UART
- Analog: ratiometric or absolute
- Switching output
- Temperature output

Capacitive ceramic pressure transducer

Ceracore UTC30

Capacitive ceramic pressure transducer for absolute and gauge pressure measurement based on the USC30 sensor.

Design size

- External diameter: ≥22 mm
- Length depends on mechanical design
- Various process connections selectable*

Standardized measuring ranges

- 0...100 mbar / 10 kPa / 1.5 psi, overload range: 4 bar / 400 kPa / 60 psi
- 0...200 mbar / 20 kPa / 3 psi, overload range: 5 bar / 500 kPa / 75 psi
- 0...400 mbar / 40 kPa / 6 psi, overload range: 6 bar / 600 kPa / 90 psi
- 0...1 bar / 100 kPa / 15 psi, overload range: 10 bar / 1 MPa / 150 psi
- 0...2 bar / 200 kPa / 30 psi, overload range: 18 bar / 1.8 MPa / 270 psi
- 0...4 bar / 400 kPa / 60 psi, overload range: 25 bar / 2.5 MPa / 375 psi
- 0...10 bar / 1 MPa / 150 psi, overload range: 40 bar / 4 MPa / 600 psi
- 0...20 bar / 2 MPa / 300 psi, overload range: 40 bar / 4 MPa / 600 psi
- 0...40 bar / 4 MPa / 600 psi, overload range: 60 bar / 6 MPa / 900 psi
- 0...100 bar / 10 MPa / 1500 psi, overload range: 150 bar / 15 MPa / 2250 psi**

Operating conditions

- Process temperature range: -20...+80°C (extended temperature range* -40...+125°C)
- Ambient temperature range: -20...+80°C (extended temperature range* -40...+125°C)
- Storage temperature range: -40 ...+125°C
- Turndown possible up to 5:1***

Output signal and power supply

- Supply voltage: 2.9 to 5.5 V DC
- Current consumption: <1.6mA
- Ratiometric or absolute analog output signal
- Digital interface: UART or SPI
- Print signal: 24 bit
- Temperature signal (optional): 16 bit
- Measurement rate: 1.25 to 80 ms
- Reference accuracy: ≤0.1 %



* On request according to technical specification (TI)

** In preparation

*** Specifications at turn-down according to Technical Specification (TI)





The MySensor concept: Your choice

Process adaption

You may choose from all common process connections and the most varied sealings. The completed pressure transducer must finally fit into your product. We help you to achieve this objective. There are almost no limits in relation to the external form of the pressure sensor.

Measuring range

Employing technology, you can measure pressure ranges from 100 mbar to 100 bar of absolute or gauge pressure. Customized measuring ranges may be factory set. The performance of the sensor can be adjusted to your application – you get what you need.

Electric connection

You may choose from different connection options (plug/cable). Select also from the various output signals – analog or digital.

Additional options

In many industries, certification and approvals plays a decisive role. Select from different certification options and order final inspection protocols, certificates and documentation.





The MySensor concept: Our configurator

Take advantage of the modular options and create your version of your sensor with our configurator. After a few clicks you will receive a transducer that will meet your expectations and is tailored exactly to your application. Based on the first configuration we work out your final pressure transducer together with you.





More information: www.sensors-components.endress.com /configurator

Silicon differential pressure sensor

The differential pressure sensors Deltacore USD50(B) and USD70 are the base for building high-quality differential pressure transmitters. The piezoresistive sensors with welded metal diaphragm are typically used in the process and environmental industries. Applications are level, volume or mass measurement in liquids, differential pressure monitoring (e.g. of filters and pumps) as well as flow measurement (volume or mass flow). The sensors are uncompensated and can be compensated and calibrated by the customer for the relevant application.





Technology



Sensor cross section Deltacore USD70

Silicon differential pressure sensor

Deltacore USD50(B)

Differential pressure sensor for a variety of applications.

Your benefits

- Silicon differential pressure sensor
- Uncompensated bridge output signal (mV) with stranded cable
- Measuring ranges from 100 mbar to 40 bar
- High accuracy, reproducibility and long-term stability
- Version in 316L (stainless steel)
- Various diaphragm materials and filling oils could be selected
- High overload resistance of 160/420 bar (on one side)
- 240/630 bar (both sides)*

Design size

Ø 55 mm x 40 mm

Standardized measuring ranges

- 0...100 mbar / 10 kPa / overload range: 160 bar (one side), 240 bar (both sides)
- 0...500 mbar / 50 kPa / overload range: 160 bar (one side), 240 bar (both sides)
- 0...3 bar / 300 kPa / overload range: 160 bar (one side), 240 bar (both sides)
- 0...16 bar / 1.6 MPa / overload range: 160 bar (one side), 240 bar (both sides)
- 0...40 bar / 4 MPa / overload range: 160 bar (one side), 240 bar (both sides)

An increased overload range of 420 bar (one side*), 630 bar (both sides*) is available as an option.

Operating conditions

- Process temperature range: -40...+85°C
- Ambient temperature range: -40...+85°C
- Storage temperature range: -40...+85°C

Output signal and power supply

- Recommended: Constant current supply <1 mA</p>
- Bridge resistance: 4.3...5.6 kΩ (25°C)



Deltacore USD70

Differential pressure sensor for small measuring ranges with high overload resistance.

Your benefits

- Silicon differential pressure sensor
- Uncompensated bridge output signal (mV)
- Measuring ranges 10 mbar and 30 mbar
- High accuracy, reproducibility and long-term stability
- Version in 316L (stainless steel)
- Various diaphragm materials and filling oils can be selected
- High overload resistance

Design size

Ø 55 mm x 40 mm

Standardized measuring ranges

- 0...10 mbar / 1 kPa / overload range: 160 bar (one side), 240 bar (both sides)
- 0...30 mbar / 3 kPa / overload range: 160 bar (one side), 240 bar (both sides)

Operating conditions

- Process temperature range: -40...+85°C
- Ambient temperature range: -40...+85°C
- Storage temperature range: -40...+85°C

Output signal and power supply

- Recommended: Constant current supply <1 mA
- Bridge resistance: 4.5...5.6 kΩ (25°C)
- Output signal:
 - 10 mbar / ±13.8 mV/V (span)
 - 30 mbar / ±25 mV/V (span)



Radar module UTR30 and radar sensor USR30: Simple implementation with a wide range of possible uses

With the free-radiating radar module UTR30, we offer you a real all-rounder, which is particularly suitable for level monitoring in liquids or solids. The continuous, non-contact measurement according to the time-of-flight principle enables precise measurement in tanks and silos up to 15m deep as well as the measurement of water levels. In addition, the radar measurement technology is ideally suited to coping with challenges such as movements in the tank, rapid temperature changes or rough weather conditions. The UTR30 is available in various versions from a pure sensor to a customer-specific radar module with a defined electrical interface.



country-specific requirementsRoHS compliant (back of module can be welded or screwed)



The radar sensor USR30 is the smallest size of the new radar sensors. It offers complete functionality of the UTR30, however, without housing and without predetermined, ready-made electrical connection. The output signal becomes digital (UART) output and can application-related to the use in the target application.

Application-specific configuration

- Housing design
- Electrical connection (M12, cable outlet, etc.)*
- Process connection*
 - G 1 ½″
 - MNPT 1 1/2"
- Optionally selectable communication interfaces

*further options on request



Technology/parameterization

- Time-of-Flight method (ToF)
- Radar (80GHz)
- Easy parametrization:
 - Medium (solid/liquid)
 - Sensitivity (low/medium/high) dependent on turbulence such as dust or waves



Calibration parameter R: Reference point BD: Blocking distance E: Empty calibration (zero)

F: Full calibration (=span) D: Measured distance L: Level (L=E-D)

Applications

Your specifications count, irrespective of the industry

The high product quality of sensors and components and the pertaining precision and durability reduce costs during the entire life cycle of your product and underline the claim of your products concerning reliability and safety. We are at home in the following industries, have profound knowledge of requirements at our disposal, guarantee safety and offer you qualified support.



Energy

Environment



Shipbuilding



Life Sciences

Medical Technology

The Endress+Hauser Group

Endress+Hauser is a global leader in measurement instrumentation, services and solutions for industrial process engineering. The Group employs 15,000 personnel across the globe, generating net sales of more than 2.9 billion euros in 2021.

Structure

With dedicated sales centers and a strong network of partners, Endress+Hauser guarantees competent worldwide support. Our production centers in 12 countries meet customers' needs and requirements quickly and effectively. The Group is managed and coordinated by a holding company in Reinach, Switzerland. As a successful family-owned business, Endress+Hauser is set for continued independence and self-reliance.

Products

Endress+Hauser provides sensors, instruments, systems and services for level, flow, pressure and temperature measurement as well as analytics and data acquisition. The company supports customers with automation engineering, logistics and IT services and solutions. Our products set standards in quality and technology.

Industries

We work closely with the chemical, petrochemical, food & beverage, oil & gas, water & wastewater, power & energy, life science, primaries & metal, renewable energies, pulp & paper and shipbuilding industries. Endress+Hauser supports its customers in optimizing their processes in terms of reliability, safety, economic efficiency and environmental impact.



Endress+Hauser SE+Co. KG Business Area Sensors&Components

Endress+Hauser LP DE Hauptstraße 1 79689 Maulburg Germany

Phone: +49 7622 28 2147 Mailto: sensors-components.pcm@endress.com www.sensors-components.endress.com Endress+Hauser LP CN Singapore Industrial Park (SIP) Su Hong Zhong Road, No. 491 215021 Suzhou, P.R. China

Phone: +86 512 62584226 Mailto: sensors-components.pcm@endress.com www.sensors-components.endress.com Endress+Hauser LP US 2340 Endress Place Greenwood Indiana 46143, USA

Phone: +1 317 535 2774 Mailto: sensors-components.pcm@endress.com www.sensors-components.endress.com

